



# External RBIAS Resistor (R1) Revision for ADL8112

# Data Sheet Specification Comparison

## Rev 0

**Table 13. Recommended Bias Resistor Values at  $V_{DD1} = 8.5\text{ V}$**

$R_{BIAS}$ ( $\Omega$ )	$I_{DQ}$ (mA)	$I_{DQ\_AMP}$ (mA)	$I_{RBIAS}$ (mA)
168	100	77	23
332	90	80	10
554	80	72	8
908	70	64	6
1455	60	56	4

## Rev A

**Table 13. Recommended Bias Resistor Values at  $V_{DD1} = 8.5\text{ V}$**

$R_{BIAS}$ ( $\Omega$ )	$I_{DQ}$ (mA)	$I_{DQ\_AMP}$ (mA)	$I_{RBIAS}$ (mA)
537	100	91.4	8.6
750	90	83	7
945	80	74	6
1278	70	65.2	4.8
1783	60	56.3	3.7