


SIZE	QTY	SYM	PLTD
95	6	+	PLTD
35	3	X	PLTD
15	23	□	PLTD
70	2	◇	NPLTD


NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISHED ON 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003
INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING:



8. L2 AND L3 ARE IDENTICLE

REVISIONS		
REV	DESCRIPTION	DATE

APPROVALS			 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 Phi: (408)432-1900	
DRAWN	INIT	DATE				
CHECK						
DESIGN	JUNE WU	4/30/02	TITLE:			
ENGR	FRAN H.	4/30/02	LTC4050EMS Li-Ion Battery Charger with NTC			
			SIZE	DEMO	REV.	A
				A	DC530A	
SCALE = NONE			DES-230551		SHT 1 of 1	