

**LINEAR TECHNOLOGY MATERIALS DECLARATION**

1t3011edd#pbf

(Engineering Calculation)

DFN 3mm X 3mm Exp. Pad

(printed on: 2020-07-11 20:23:44)

**TOTAL MASS (g) : 0.02367**

| COMPONENT MATERIAL             | VENDOR/ INDUSTRY NAMES           | CONSTITUENT NAME               | CAS NUMBER | CONSTITUENT MASS (g) | CONSTITUENT (PPM) OF MATERIAL | CONSTITUENT (PPM) OF TOTAL PKG. |                |                      |
|--------------------------------|----------------------------------|--------------------------------|------------|----------------------|-------------------------------|---------------------------------|----------------|----------------------|
| Active Device                  | Linear Technology                | Silicon (Si)                   | 7440-21-3  | 0.001510             | 1000000                       | 63792.8554688                   |                |                      |
| Die Coat                       | Dow Corning                      | Silicone                       | 69430-27-9 | 0.000000             | 0                             | 0                               |                |                      |
| Lead Frame                     | Cu                               | Copper (Cu)                    | 7440-50-8  | 0.009711             | 975000                        | 410259.875                      |                |                      |
|                                |                                  | Iron (Fe)                      | 7439-89-6  | 0.000239             | 24000                         | 10097.0146484                   |                |                      |
|                                |                                  | Phosphorus (P)                 | 7723-14-0  | 0.000003             | 300                           | 126.740776062                   |                |                      |
|                                |                                  | Zinc (Zn)                      | 7440-66-6  | 0.000007             | 700                           | 295.728485107                   |                |                      |
|                                |                                  | Nickel (Ni)                    | 7440-02-0  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Silicon (Si)                   | 7440-21-3  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Magnesium (Mg)                 | 7439-95-4  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Tin (Sn)                       | 7440-31-5  | 0.000000             | 0                             | 0                               |                |                      |
| <b>Lead Frame Total:</b>       |                                  |                                |            | <b>0.009960</b>      | <b>1000000</b>                | <b>420779.375</b>               |                |                      |
| Plating                        | PMI                              | Exter. Plating Pb              | 7439-92-1  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Exter. Plating Sn              | 7440-31-5  | 0.000455             | 1000000                       | 19237.6738281                   |                |                      |
|                                |                                  | <b>External Plating Total:</b> |            |                      |                               | <b>0.000455</b>                 | <b>1000000</b> | <b>19237.6738281</b> |
|                                |                                  | Inter. Plating Ni              | 7440-02-0  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Inter. Plating Ag              | 7440-22-4  | 0.000225             | 1000000                       | 9505.55761719                   |                |                      |
| <b>Internal Plating Total:</b> |                                  |                                |            | <b>0.000225</b>      | <b>1000000</b>                | <b>9505.55761719</b>            |                |                      |
| Die Attach                     | ELECTRICALLY CONDUCTIVE ADHESIVE | Silver (Ag)                    | 7440-22-4  | 0.000750             | 750000                        | 31685.1914062                   |                |                      |
|                                |                                  | Tin (Sn)                       | 7440-31-5  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Lead (Pb)                      | 7439-92-1  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Silica (SiO2)                  | 60676-86-0 | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Indium (In)                    | 7440-74-6  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Metal Oxide                    |            | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Antimony (Sb)                  | 7440-36-0  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Resin (EP)                     |            | 0.000250             | 250000                        | 10561.7314453                   |                |                      |
| <b>Die Attach Total:</b>       |                                  |                                |            | <b>0.001000</b>      | <b>1000000</b>                | <b>42246.9257812</b>            |                |                      |
| Encapsulation                  | FILLED EPOXY RESIN               | Resin (EP)                     |            | 0.001153             | 110000                        | 48710.703125                    |                |                      |
|                                |                                  | Bromine (Br)                   | 40039-93-8 | 0.000105             | 10000                         | 4435.92724609                   |                |                      |
|                                |                                  | Silica (SiO2)                  | 60676-86-0 | 0.008908             | 850000                        | 376335.59375                    |                |                      |
|                                |                                  | Antimony Trioxide (Sb2O3)      | 1309-64-4  | 0.000314             | 30000                         | 13265.5341797                   |                |                      |
|                                |                                  | Metal Hydroxide                |            | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Carbon Black (C)               | 1333-86-4  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | <b>Encapsulation Total:</b>    |            |                      |                               | <b>0.010480</b>                 | <b>1000000</b> | <b>442747.75</b>     |
| Bond Wire Estimated            | AFW/TANAKA/ Kn                   | Gold (Au)                      | 7440-57-5  | 0.000040             | 1000000                       | 1689.87695312                   |                |                      |
|                                |                                  |                                |            |                      | <b>TOTAL MASS (g) :</b>       | <b>0.02367</b>                  |                |                      |