




TOP VIEW



BOTTOM VIEW



SIDE VIEW



TITLE:
PACKAGE OUTLINE, 20L eMGA,
3.5x3.5x1.55mm

APPROVAL
TANYE TANG

DOCUMENT CONTROL NO.
21-100447

REV. D 1/2

-DRAWING NOT TO SCALE-

SYMBOL	20L 3.5x3.5			NOTE
	MIN.	NOM.	MAX.	
A	1.30	1.55	1.8	
A1	0.25	0.41	0.57	
b	0.20	0.25	0.30	
c	0.025	0.075	0.125	
D	3.40	3.50	3.60	
D2	1.75	1.80	1.85	
E	3.40	3.50	3.60	
E2	1.75	1.80	1.85	
ⓔ	0.50 BSC			
F	2.50 REF			
G	2.00 REF			
L1	0.35	0.40	0.45	
N	20			2

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. "N" IS THE TOTAL NUMBER OF TERMINALS.
3. ALL DIMENSIONS AND TOLERANCES CONFORM TO ANSI Y14.5M-1994.
4. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC #10-0131.
5. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
6. PACKAGE CODE: M203A3+1
7. REFER TO 73-100015 FOR PACKAGE DRAWING FOR INTERNAL HARDWARE TOOLING

 maxim integrated.			
TITLE: PACKAGE OUTLINE, 20L eMGA, 3.5x3.5x1.55mm			
APPROVAL	DOCUMENT CONTROL NO.	REV.	2/2
TANYE TANG	21-100447	D	

-DRAWING NOT TO SCALE-