



Certificate of Compliance

Certificate: 2638205

Master Contract: 205078

Project: 80116749

Date Issued: 2022-04-21

Issued To: Analog Devices Inc.
804 Woburn St
Wilmington, Massachusetts, 01887-3462
United States

Attention: James Scanlon

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator ▲



Issued by: Martin Buchanan
Martin Buchanan, P. Eng.

PRODUCTS

CLASS - C907330 - ELECTRONIC COMPONENTS Optoisolators and non-optical isolating devices

Component Acceptance of Optoisolator Like Magnetic Coupling Devices:

Device (SOIC 16W RI package)	Ratings		Clauses of Standard/Notice	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ADuM4470xRIZ ADuM4471xRIZ ADuM4472xRIZ ADuM4473xRIZ ADuM4474xRIZ	5.0	105	CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 62368-1-19 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC	-	-	8.7



Certificate: 2638205
Project: 80116749

Master Contract: 205078
Date Issued: 2022-04-21

Device (SOIC 16W RI package)	Ratings		Clauses of Standard/Notice	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			62368-1:2018 Ed. 3 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 62368-1:2020+A11:2020 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4			

where x is a letter representing data rate and Z, if used, indicates the lead-free version. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

Notes:

1. These devices meet basic insulation requirements for 870Vrms for CSA 62368-1:19. IEC 62368-1:2018 Ed. 3 and EN62368-1:2020+A11:2020. (pollution degree 2, material group III)
2. These devices meet reinforced insulation requirements for 435Vrms for CSA 62368-1:19. IEC 62368-1:2018 Ed. 3 and EN62368-1:2020+A11:2020. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. for 600Vrms for basic insulation and 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 1 MOPP for 544Vrms, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
5. Case material: Mold compound meets material group II.
- 6 Evaluated by thermal cycling and other tests for a temperature rating of 105C.
7. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

- | | |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| CAN/CSA-C22.2 No 14-18 | - Industrial Control Equipment |
| CAN/CSA-C22.2 No. 62368-1:19 | - Audio/video, information and communication technology equipment - Part 1: Safety requirements (Bi-national Standard with ANSI/UL 62368-1-2019) |
| IEC 62368-1:2018 Ed. 3 | - Audio/video, information and communication technology equipment - Part 1: Safety requirements |



Certificate: 2638205
Project: 80116749

Master Contract: 205078
Date Issued: 2022-04-21

EN 62368-1:2020+A11:2020 - Audio/video, information and communication technology equipment - Part 1: Safety requirements (IEC 62368-1:2018)

Clauses 6.7.1.3, 6.7.2.1 or K.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 of
 CAN/CSA C22.2 No. 61010-1-12, UPD1: 2015, UPD2: 2016, AMD1: 2018 - Safety Requirements for Electrical Equipment for Measurement, Control, and Laboratory Use, Part 1: General Requirements (Tri-national standard, with UL 61010-1 Ed. 3 (2012), AMD1: 2018 and ANSI/ISA-61010-1 (82.02.01))

IEC 61010-1:2010 Ed. 3.1:2017 01 - Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements

Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7
 of

CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety and general performance (Adopted IEC60601-1:2005 Edition 3.0 +Amendment 1, 2012-07, MOD)

and
 IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic safety and general performance

Notes:

Products certified under Class C907330 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). www.scc.ca





Supplement to Certificate of Compliance

Certificate: 2638205

Master Contract: 205078

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
80116749	2022-04-21	Update to 2638205 for 62368-1 Ed 3
70046794	2016-10-26	Update for alternative mould compound and leadframe
2638205	2013-12-11	Original Component Acceptance