



Certificate of Compliance

Certificate: 70051667 **Master Contract:** 205078 (205078)
Project: 70168150 **Date Issued:** 2018-01-15
Issued to: Analog Devices Inc.
 804 Woburn St
 Wilmington, Massachusetts 01887-3462
 USA
 Attention: Mark Cantrell

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator ▲



Issued by: *Martin Buchanan*
 Martin Buchanan, P. Eng.

PRODUCTS

CLASS - C907330 - ELECTRONIC COMPONENTS-Optoisolators

Component Acceptance of Optoisolator Like Magnetic Coupling Devices:

Device	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
(SOIC 16W RW package) ADuM4135BRWZ ADuM4136BRWZ	5.7	125	CSA 14-13 Tbl 35, 6.2.1.1, 6.2.1.1/6.2.10, 6.8.1.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1-12+A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2	-	-	7.8



Certificate: 70051667
Project: 70168150

Master Contract: 205078
Date Issued: 2018-01-15

Device	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			61010-1 3 rd Ed A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2			
(SOIC 16W RI package) ADuM4136BRIZ	5.0	125	CSA 14-13 Tbl 35, 6.2.1.1, 6.2.1.1/6.2.10, 6.8.1.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1-12+A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1 3 rd Ed A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2	-	-	8.3

where Z, if used, indicates the lead-free version. Further suffix letters or digits differentiate shipping package formats. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish.

Notes:

1. The RW devices meet basic insulation requirements for 780Vrms and RI devices meet 830Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14 and IEC 60950-1 2nd Ed.+A1+A2 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
2. The RW devices meet reinforced insulation requirements for 390Vrms and RI devices meet 415Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14 and IEC 60950-1 2nd Ed.+A1+A2 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. for 600Vrms, overvoltage category III for RW devices and overvoltage category IV for RI devices for basic insulation, the devices meet clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2



Certificate: 70051667
Project: 70168150

Master Contract: 205078
Date Issued: 2018-01-15

- A.17, K.6x1.6, K.7x1.6, 10. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. the RW and RI devices meet 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. (pollution degree 2, material group III)
5. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 2 MOPP for 237.5Vrms for RW devices and 250V for RI devices, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
6. Case material: 575Vrms with erosion depth 0.079mm, meets material group II.
7. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
8. The creepage and clearance has been evaluated for altitudes $\leq 2000m$, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

- CAN/CSA-C22.2 No 14-13 - Industrial Control Equipment
- CAN/CSA-C22.2 No 60950-1-07+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements (Bi-national Standard, with UL 60950-1)
- CAN/CSA-C22.2 No. 62368-1-14 - Audio/video, information and communication technology equipment– Part 1: Safety requirements
- IEC 60950-1 2nd Ed.+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- IEC 62368-1:2014 Ed. 2 - Audio/video, information and communication technology equipment– Part 1: Safety requirements
- EN 60950-1:2006+A1+A12+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- Clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10
of
CAN/CSA-C22.2 No. 61010-1-12+A1 2015 - Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements (Tri-national standard, with UL 61010-1 Ed. 3 and ANSI/ISA-61010-1 (82.02.01)
- and
IEC 61010-1:2010 3rd Ed. - Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements
- Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7
of



Certificate: 70051667

Project: 70168150

Master Contract: 205078

Date Issued: 2018-01-15

- CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety and general performance (Adopted IEC60601-1:2005 Edition 3.0 +Amendment 1, 2012-07, MOD)
- and
- IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic safety and general performance



Supplement to Certificate of Compliance

Certificate: 70051667

Master Contract: 205078 (205078)

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
70168150	2018-01-15	Update to add ADuM4136BRWZ, ADuM4136BRIZ
70051667	2016-08-05	Original Component Acceptance