



# Certificate of Compliance

**Certificate:** 70137642 **Master Contract:** 205078 (205078)  
**Project:** 70137642 **Date Issued:** 2018-02-13  
**Issued to:** Analog Devices Inc.  
 804 Woburn St  
 Wilmington, Massachusetts 01887-3462  
 USA  
 Attention: Mark Cantrell

*The products listed below are eligible to bear the CSA Mark shown with adjacent indicator ▲*



**Issued by:** Martin Buchanan  
 Martin Buchanan, P. Eng.

## **PRODUCTS**

CLASS - C907330 - ELECTRONIC COMPONENTS-Optoisolators

Component Acceptance of Optoisolator Like Magnetic Coupling Devices:

Device (SOIC 24W package)	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ADP1074ARWZ	5.0	125	CSA 14-13 Tbl 35, 6.2.1.1, 6.2.1.1/6.2.10, 6.8.1.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1-12+A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2	-	-	7.8



**Certificate:** 70137642

**Master Contract:** 205078

**Project:** 70137642

**Date Issued:** 2018-02-13

Device (SOIC 24W package)	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			61010-1 3 <sup>rd</sup> Ed A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2			

where Z, if used, indicates the lead-free version. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

**Notes:**

1. These devices meet basic insulation requirements for 780Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14, IEC 60950-1 2<sup>nd</sup> Ed.+A1+A2 and IEC 62368-1 2<sup>nd</sup> Ed. (pollution degree 2, material group III)
2. These devices meet reinforced insulation requirements for 390Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14, IEC 60950-1 2<sup>nd</sup> Ed.+A1+A2 and IEC 62368-1 2<sup>nd</sup> Ed. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3<sup>rd</sup> Ed. for 600Vrms, overvoltage category III for basic insulation the devices meet clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. For CSA 61010-1-12+A1 and IEC 61010-1 3<sup>rd</sup> Ed. these devices meet 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. (pollution degree 2, material group III)
5. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 2 MOPP for 237.5Vrms, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
6. Case material: 575Vrms with erosion depth 0.079mm, meets material group II.
7. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
8. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

**APPLICABLE REQUIREMENTS**

- CAN/CSA-C22.2 No 14-13 - Industrial Control Equipment
- CAN/CSA-C22.2 No 60950-1-07+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements (Bi-national Standard, with UL 60950-1)
- CAN/CSA-C22.2 No. 62368-1-14 - Audio/video, information and communication technology equipment– Part 1: Safety requirements



**Certificate:** 70137642

**Project:** 70137642

**Master Contract:** 205078

**Date Issued:** 2018-02-13

IEC 60950-1 2<sup>nd</sup> Ed.+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements  
IEC 62368-1:2014 Ed. 2 - Audio/video, information and communication technology equipment- Part 1: Safety requirements

EN 60950-1:2006+A1+A12+A2 - Information Technology Equipment - Safety - Part 1: General Requirements

Clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10  
of

CAN/CSA-C22.2 No. 61010-1-12+A1 2015 - Safety Requirements for Electrical Equipment for  
Measurement, Control and Laboratory Use - Part 1: General Requirements  
(Tri-national standard, with UL 61010-1 Ed. 3 and ANSI/ISA-61010-1  
(82.02.01))

and

IEC 61010-1:2010 3<sup>rd</sup> Ed. - Safety Requirements for Electrical Equipment for Measurement, Control  
and Laboratory Use - Part 1: General Requirements

Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  
of

CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety  
and general performance (Adopted IEC60601-1:2005 Edition 3.0  
+Amendment 1, 2012-07, MOD)

and

IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic  
safety and general performance



## *Supplement to Certificate of Compliance*

**Certificate:** 70137642

**Master Contract:** 205078 (205078)

*The products listed, including the latest revision described below,  
are eligible to be marked in accordance with the referenced Certificate.*

### **Product Certification History**

---

<b>Project</b>	<b>Date</b>	<b>Description</b>
70137642	2018-02-13	Original Component Acceptance