

**LINEAR TECHNOLOGY MATERIALS DECLARATION**

1t1227cn8#pbf

(Engineering Calculation)

PDIP

(printed on: 2020-07-11 19:19:52)

**TOTAL MASS (g) : 0.497707**

| COMPONENT MATERIAL             | VENDOR/ INDUSTRY NAMES           | CONSTITUENT NAME               | CAS NUMBER | CONSTITUENT MASS (g) | CONSTITUENT (PPM) OF MATERIAL | CONSTITUENT (PPM) OF TOTAL PKG. |                |                      |
|--------------------------------|----------------------------------|--------------------------------|------------|----------------------|-------------------------------|---------------------------------|----------------|----------------------|
| Active Device                  | Linear Technology                | Silicon (Si)                   | 7440-21-3  | 0.001232             | 1000000                       | 2475.3503418                    |                |                      |
| Die Coat                       | Dow Corning                      | Silicone                       | 69430-27-9 | 0.000000             | 0                             | 0                               |                |                      |
| Lead Frame                     | Cu                               | Copper (Cu)                    | 7440-50-8  | 0.149760             | 975000                        | 300899.75                       |                |                      |
|                                |                                  | Iron (Fe)                      | 7439-89-6  | 0.003686             | 24000                         | 7405.95947266                   |                |                      |
|                                |                                  | Phosphorus (P)                 | 7723-14-0  | 0.000046             | 300                           | 92.4238052368                   |                |                      |
|                                |                                  | Zinc (Zn)                      | 7440-66-6  | 0.000108             | 700                           | 216.995010376                   |                |                      |
|                                |                                  | Nickel (Ni)                    | 7440-02-0  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Silicon (Si)                   | 7440-21-3  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Magnesium (Mg)                 | 7439-95-4  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Tin (Sn)                       | 7440-31-5  | 0.000000             | 0                             | 0                               |                |                      |
| <b>Lead Frame Total:</b>       |                                  |                                |            | <b>0.153600</b>      | <b>1000000</b>                | <b>308615.15625</b>             |                |                      |
| Plating                        | PMI                              | Exter. Plating Pb              | 7439-92-1  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Exter. Plating Sn              | 7440-31-5  | 0.012410             | 1000000                       | 24934.9199219                   |                |                      |
|                                |                                  | <b>External Plating Total:</b> |            |                      |                               | <b>0.012410</b>                 | <b>1000000</b> | <b>24934.9199219</b> |
|                                |                                  | Inter. Plating Ni              | 7440-02-0  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Inter. Plating Ag              | 7440-22-4  | 0.001228             | 1000000                       | 2467.3137207                    |                |                      |
| <b>Internal Plating Total:</b> |                                  |                                |            | <b>0.001228</b>      | <b>1000000</b>                | <b>2467.3137207</b>             |                |                      |
| Die Attach                     | ELECTRICALLY CONDUCTIVE ADHESIVE | Silver (Ag)                    | 7440-22-4  | 0.000501             | 750000                        | 1006.61572266                   |                |                      |
|                                |                                  | Tin (Sn)                       | 7440-31-5  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Lead (Pb)                      | 7439-92-1  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Silica (SiO2)                  | 60676-86-0 | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Indium (In)                    | 7440-74-6  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Metal Oxide                    |            | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Antimony (Sb)                  | 7440-36-0  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Resin (EP)                     |            | 0.000167             | 250000                        | 335.538604736                   |                |                      |
| <b>Die Attach Total:</b>       |                                  |                                |            | <b>0.000668</b>      | <b>1000000</b>                | <b>1342.15441895</b>            |                |                      |
| Encapsulation                  | FILLED EPOXY RESIN               | Resin (EP)                     |            | 0.078816             | 240000                        | 158358.140625                   |                |                      |
|                                |                                  | Bromine (Br)                   | 40039-93-8 | 0.003284             | 10000                         | 6598.25585938                   |                |                      |
|                                |                                  | Silica (SiO2)                  | 60676-86-0 | 0.236448             | 720000                        | 475074.4375                     |                |                      |
|                                |                                  | Antimony Trioxide (Sb2O3)      | 1309-64-4  | 0.009852             | 30000                         | 19794.7675781                   |                |                      |
|                                |                                  | Metal Hydroxide                |            | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | Carbon Black (C)               | 1333-86-4  | 0.000000             | 0                             | 0                               |                |                      |
|                                |                                  | <b>Encapsulation Total:</b>    |            |                      |                               | <b>0.328400</b>                 | <b>1000000</b> | <b>659825.5625</b>   |
| Bond Wire Estimated            | AFW/TANAKA/ Kn                   | Gold (Au)                      | 7440-57-5  | 0.000169             | 1000000                       | 339.557037354                   |                |                      |
|                                |                                  |                                |            |                      | <b>TOTAL MASS (g) :</b>       | <b>0.497707</b>                 |                |                      |