





**LQFN Package**  
**24-Lead (3.5mm × 4mm × 0.95mm)**  
 (Reference DWG # 05-08-7065)



DIMENSIONS				
SYMBOL	MIN	NOM	MAX	NOTES
A	0.85	0.95	1.05	
A1			0.04	
L1	0.30	0.40	0.50	
L2	0.36	0.46	0.56	
b	0.22	0.25	0.28	
D		3.50		
E		4.00		
D1		2.08		
E1		2.70		
e		0.50		
H1		0.25 REF		SUBSTRATE THK
H2		0.70 REF		MOLD CAP HT
aaa			0.10	
bbb			0.10	
ccc			0.10	
ddd			0.10	
eee			0.15	
fff			0.08	

- NOTES:**
- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994**
  - 2. ALL DIMENSIONS ARE IN MILLIMETERS**
  - 3. PRIMARY DATUM -Z- IS SEATING PLANE**
  - 4. METAL FEATURES UNDER THE SOLDER MASK OPENING NOT SHOWN SO AS NOT TO OBSCURE THESE TERMINALS AND HEAT FEATURES**
  - 5. DETAILS OF PIN 1 IDENTIFIER ARE OPTIONAL, BUT MUST BE LOCATED WITHIN THE ZONE INDICATED. THE PIN 1 IDENTIFIER MAY BE EITHER A MOLD OR MARKED FEATURE**
  - 6. THE EXPOSED HEAT FEATURE IS SEGMENTED AND ARRANGED IN A MATRIX FORMAT. IT MAY HAVE OPTIONAL CORNER RADII ON EACH SEGMENT**

