





DOCUMENT TYPE: POD
DOCUMENT ID #: 21-100682
REVISION: A-000
DOCUMENT TITLE: PACKAGE OUTLINE 42 BUMPS THIN WLP PKG. 0
EFFECTIVE DATE: 08/29/2022
EXPIRATION DATE:
CHANGE NUMBER: 1169803
ORIGINATOR: Merla Avendano

REASON FOR CHANGE:
S18 8" 0.35mmp 7x6 thin WLP NPI for I&H



COMMON DIMENSIONS	
A	0.50 MAX
A1	0.16 ±0.03
A2	0.31 REF
A3	0.04 BASIC
b	∅0.22 ±0.03
D	2.468 ±0.025
E	2.778 ±0.025
D1	1.75 BASIC
E1	2.10 BASIC
e	0.35 BASIC
SD	0.175 BASIC
SE	0.00 BASIC
DEPOPULATED BUMPS: NONE	



- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.
 5. Tolerance is ± 0.02 unless specified otherwise.
 6. All dimensions apply to PbFree (+) package codes only.
 7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -

TITLE PACKAGE OUTLINE 42 BUMPS THIN WLP PKG. 0.35 mm PITCH, N422B2+1			
APPROVAL	DOCUMENT CONTROL NO.	REV.	1/1
	21-100682	A	

REVISION HISTORY

REV	CHANGES MADE	DATE	INIT.
A	CN 1169803. INITIAL RELEASE. S18 8" 0.35mmp 7x6 thin WLP NPI for I&H.	08/29/22	MA

TITLE: PACKAGE OUTLINE 42 BUMPS THIN WLP PKG. 0.35 mm PITCH, N422B2+1

DOCUMENT I.D.
21-100682

REVISION
A

PAGE
2

