



Certificate of Compliance

Certificate: 80020410

Master Contract: 205078

Project: 80020410

Date Issued: 2020-03-31

Issued To: Analog Devices Inc.
804 Woburn St
Wilmington, Massachusetts, 01887-3462
United States

Attention: Mark Cantrell

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator▲



Issued by: *Martin Buchanan*
Martin Buchanan, P. Eng.

PRODUCTS

CLASS - C907330 - ELECTRONIC COMPONENTS Optoisolators and non-optical isolating devices

Component Acceptance of Optoisolator Like Devices:

Device	Ratings		Standard/Notice and Clauses	Internal		External
	(kV)	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
SOIC 8W (RI-8-1) ADM3050EBRIZ ADM3050EWBRIZ	5.7	125	CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10	-	-	8.3



Certificate: 80020410
Project: 80020410

Master Contract: 205078
Date Issued: 2020-03-31

Device	Ratings		Standard/Notice and Clauses	Internal		External
	(kV)	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014/A11:2017 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3			
SOIC 16W (RW-16) ADM3050EBRWZ ADM3050EWBRWZ	5.7	125	CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10	-	-	7.8



Certificate: 80020410
Project: 80020410

Master Contract: 205078
Date Issued: 2020-03-31

Device	Ratings		Standard/Notice and Clauses	Internal		External
	(kV)	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014/A11:2017 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3			
SOIC 16W (RI-16) ADM3056EBRIZ ADM3056EWBRIZ	5.7	125	CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014/A11:2017 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 5.4.8, 5.4.1.4, 5.4.3.3	-	-	8.3

where Z if used indicates the lead-free version. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.



Certificate: 80020410
Project: 80020410

Master Contract: 205078
Date Issued: 2020-03-31

Notes:

1. The RI devices meet basic insulation requirements for 830Vrms and reinforced insulation requirements for 415Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14. IEC 60950-1 2nd Ed.+A1+A2, IEC 62368-1:2014 and EN60950-1:2006+A1+A12+A2 and EN62368-1:2014/A11:2017. (pollution degree 2, material group III)
2. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. the RI devices meet 600Vrms for basic insulation for overvoltage category IV.
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. the RI devices meet 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 2 MOPP for 261Vrms, the RI devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
5. Case material: material group I.
6. The RW devices meet basic insulation requirements for 780Vrms and reinforced insulation requirements for 390Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14. IEC 60950-1 2nd Ed.+A1+A2, IEC 62368-1:2014 and EN60950-1:2006+A1+A12+A2 and EN62368-1:2014/A11:2017. (pollution degree 2, material group III)
7. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. the RW devices meet 600Vrms for basic insulation and 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
8. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 2 MOPP for 237.5Vrms, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
9. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
10. The creepage and clearance has been evaluated for altitudes $\leq 2000\text{m}$, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

- CAN/CSA-C22.2 No 14-18 - Industrial Control Equipment
- CAN/CSA-C22.2 No 60950-1-07+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements (Bi-national Standard, with UL 60950-1)
- CAN/CSA-C22.2 No. 62368-1-14 - Audio/video, information and communication technology equipment– Part 1: Safety requirements
- IEC 60950-1 2nd Ed.+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- IEC 62368-1:2014 Ed. 2 - Audio/video, information and communication technology equipment– Part 1: Safety requirements
- EN 60950-1:2006+A1+A12+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- EN 62368-1:2014/A11:2017 - Audio/video, information and communication technology equipment - Part 1: Safety requirements (IEC 62368-1:2014, modified)



Certificate: 80020410
Project: 80020410

Master Contract: 205078
Date Issued: 2020-03-31

Clauses 6.7.1.3, 6.7.2.1 or K.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 of
CAN/CSA C22.2 No. 61010-1-12, UPD1: 2015, UPD2: 2016, AMD1: 2018 - Safety Requirements for
Electrical Equipment for Measurement, Control, and Laboratory Use, Part
1: General Requirements (Tri-national standard, with UL 61010-1 Ed. 3
(2012), AMD1: 2018 and ANSI/ISA-61010-1 (82.02.01))

IEC 61010-1:2010 Ed. 3.1:2017 01 - Safety Requirements for Electrical Equipment for Measurement, Control
and Laboratory Use - Part 1: General Requirements

Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7
of
CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety
and general performance (Adopted IEC60601-1:2005 Edition 3.0
+Amendment 1, 2012-07, MOD)

and
IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic
safety and general performance