



RELIABILITY REPORT  
FOR  
MAX11603EEE+T  
PLASTIC ENCAPSULATED DEVICES

January 31, 2011

**MAXIM INTEGRATED PRODUCTS**

120 SAN GABRIEL DR.  
SUNNYVALE, CA 94086

<b>Approved by</b>
Richard Aburano
Quality Assurance
Manager, Reliability Operations

## Conclusion

The MAX11603EEE+T successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

## Table of Contents

I. ....Device Description	V. ....Quality Assurance Information
II. ....Manufacturing Information	VI. ....Reliability Evaluation
III. ....Packaging Information	IV. ....Die Information
.....Attachments	

### I. Device Description

#### A. General

The MAX11600-MAX11605 low-power, 8-bit, multichannel, analog-to-digital converters (ADCs) feature internal track/hold (T/H), voltage reference, clock, and an I<sup>2</sup>C-compatible 2-wire serial interface. These devices operate from a single supply and require only 350 $\mu$ A at the maximum sampling rate of 188ksps. AutoShutdown<sup>(TM)</sup> powers down the devices between conversions, reducing supply current to less than 1 $\mu$ A at low throughput rates. The MAX11600/MAX11601 provide 4 analog input channels each, the MAX11602/MAX11603 provide 8 analog input channels each while the MAX11604/MAX11605 provide 12 analog input channels. The analog inputs are software configurable for unipolar or bipolar and single-ended or pseudo-differential operation. The full-scale analog input range is determined by the internal reference or by an externally applied reference voltage ranging from 1V to VDD. The MAX11601/MAX11603/MAX11605 feature a 2.048V internal reference and the MAX11600/MAX11602/MAX11604 feature a 4.096V internal reference. The MAX11600/MAX11601 are available in 8-pin SOT23 packages. The MAX11602-MAX11605 are available in 16-pin QSOP packages. The MAX11600-MAX11605 are guaranteed over the extended industrial temperature range (-40°C to +85°C). Refer to the MAX11606-MAX11611 for 10-bit devices and to the MAX11612-MAX11617 for 12-bit devices. *Introduction to Maxim's MAX11645 family of flexible ADCs in tiny packages.*

## II. Manufacturing Information

A. Description/Function:	2.7V to 3.6V and 4.5V to 5.5V, Low-Power, 4-/8-/12-Channel, 2-Wire Serial 8-Bit ADCs
B. Process:	C6Y
C. Number of Device Transistors:	7237
D. Fabrication Location:	Japan
E. Assembly Location:	Philippines and Thailand
F. Date of Initial Production:	April 25, 2009

## III. Packaging Information

A. Package Type:	16-pin QSOP
B. Lead Frame:	Copper
C. Lead Finish:	100% matte Tin
D. Die Attach:	Conductive
E. Bondwire:	Au (1 mil dia.)
F. Mold Material:	Epoxy with silica filler
G. Assembly Diagram:	#05-9000-3655
H. Flammability Rating:	Class UL94-V0
I. Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C	Level 1
J. Single Layer Theta Ja:	120°C/W
K. Single Layer Theta Jc:	37°C/W
L. Multi Layer Theta Ja:	103.7°C/W
M. Multi Layer Theta Jc:	37°C/W

## IV. Die Information

A. Dimensions:	67 X 63 mils
B. Passivation:	Si <sub>3</sub> N <sub>4</sub> /SiO <sub>2</sub> (Silicon nitride/ Silicon dioxide)
C. Interconnect:	Al with Ti/TiN Barrier
D. Backside Metallization:	None
E. Minimum Metal Width:	0.6 microns (as drawn)
F. Minimum Metal Spacing:	0.6 microns (as drawn)
G. Bondpad Dimensions:	3.1 mil. Sq.
H. Isolation Dielectric:	SiO <sub>2</sub>
I. Die Separation Method:	Wafer Saw

## V. Quality Assurance Information

- A. Quality Assurance Contacts: Richard Aburano (Manager, Reliability Operations)  
Bryan Preeshl (Vice President of QA)
- B. Outgoing Inspection Level: 0.1% for all electrical parameters guaranteed by the Datasheet.  
0.1% For all Visual Defects.
- C. Observed Outgoing Defect Rate: < 50 ppm
- D. Sampling Plan: Mil-Std-105D

## VI. Reliability Evaluation

### A. Accelerated Life Test

The results of the 135°C biased (static) life test are shown in Table 1. Using these results, the Failure Rate ( $\lambda$ ) is calculated as follows:

$$\lambda = \frac{1}{\text{MTTF}} = \frac{1.83}{192 \times 4340 \times 48 \times 2} \quad (\text{Chi square value for MTTF upper limit})$$

(where 4340 = Temperature Acceleration factor assuming an activation energy of 0.8eV)

$$\lambda = 22.9 \times 10^{-9}$$

$\lambda = 22.9$  F.I.T. (60% confidence level @ 25°C)

The following failure rate represents data collected from Maxim's reliability monitor program. Maxim performs quarterly life test monitors on its processes. This data is published in the Reliability Report found at <http://www.maxim-ic.com/qa/reliability/monitor>. Cumulative monitor data for the C6Y Process results in a FIT Rate of 0.90 @ 25C and 15.55 @ 55C (0.8 eV, 60% UCL)

### B. E.S.D. and Latch-Up Testing (lot E2G3DA004B, D/C 0912)

The AC33-3 die type has been found to have all pins able to withstand a transient pulse of:

ESD-HBM:	+/- 2500V per JEDEC JESD22-A114
ESD-MM:	+/- 250V per JEDEC JESD22-A115

Latch-Up testing has shown that this device withstands a current of +/- 250mA and overvoltage per JEDEC JESD78.

**Table 1**  
Reliability Evaluation Test Results

**MAX11603EEE+T**

TEST ITEM	TEST CONDITION	FAILURE IDENTIFICATION	SAMPLE SIZE	NUMBER OF FAILURES	COMMENTS
<b>Static Life Test</b> (Note 1)	Ta = 135°C Biased Time = 192 hrs.	DC Parameters & functionality	48	0	E2G3DA004B, D/C 0912

Note 1: Life Test Data may represent plastic DIP qualification lots.