

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	220724	X

HOLE TOLERANCE

UNLESS SPECIFIED
PLATED: +/- 3 MILS
NON PLATED: +/- 2 MIL

DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILS				
FIGURE	SIZE	PLATED	QTY	TOLERANCE/NOTES
⊙	6.0	PLATED	7	
+	12.0	PLATED	487	
⊗	35.0	PLATED	8	
⊛	50.0	PLATED	2	
⊕	60.0	PLATED	8	
△	100.0	PLATED	13	
○	213.0	PLATED	4	
⌚	185.0	NON-PLATED	4	

TOTAL HOLES: 533

PRIMARY SIDE							
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES				APPROVAL		DATE	
TOLERANCES				TEST ENGINEER		X	
DECIMALS		FRACTIONS		ANGLES		X	
.XX . . . 010		.XXX . . . 005		.XXXX . . . 0050		.. 1/32	
.XXX . . . 005		.XXXX . . . 0050		.. 1/32		.. 2	
MATERIAL				HARDWARE SERVICES		X	
				HARDWARE SYSTEMS		X	
				TEST ENGINEER		X	
				COMPONENT ENGINEER		X	
				TEST PROCESS		X	
				HARDWARE RELEASE		X	
FINISH				DESIGNER		X	
				PID ENGINEER		X	
				CHECKER		X	
DO NOT SCALE DWG				SCALE		1/1	
				SIZE		FSCM NO	
				DRAWING NUMBER		REV	
				D 24355		A	
				09-082032		SHEET 1 OF 2	

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	220724	X

NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES (EXCEPT WHERE NOTED).
ALL DOCUMENTS & SPECIFICATIONS REFERRED TO BELOW SHOULD BE THE LATEST REVISIONS.

MATERIAL: HOMOGENOUS MATERIALS IN THIS BOARD SHALL BE COMPLAINT WITH THE EU DIRECTIVE 2002/95/EC

2. BOARD MATERIAL: (USE CHECKED ITEMS)
- () XOLA 370HR OR S1000-2 OR IT180 OR EQUIVALENT
- () ISOLA-FR408HR OR EQUIVALENT
- () ISOLA IS410
- () MEGTRON 6
- () NELCO-4000-13
- () ROGERS 4350B
- () ROGERS 3003
- () ARLON 85N
- () EM370D
- () OTHER _____

3. ALL LAMINATES & BONDING MATERIALS SHOULD BE SELECTED FROM IPC-4101 OR IPC-4103, (TG>170 DEGC TD>300 DEGC) UL FLAMMABILITY RATING 94V-0. BOARD MATERIAL & CONSTRUCTION SHALL MEET THE REQUIREMENTS OF UL796/UL796F.

4. REFER TO IPC-6010 SERIES, CLASS 2 FOR FABRICATION. WORKMANSHIP SHALL CONFORM TO IPC-A-600, CLASS 2.

5. REFER TO LAMINATION DIAGRAM FOR OVERALL BOARD THICKNESS, TOLERANCE APPLIES AFTER ALL LAMINATION AND PLATING PROCESSES. FINISHED THICKNESS MEASURED FROM TOP COPPER TO BOTTOM COPPER.

6. BOW & TWIST NOT TO EXCEED 0.0075 INCHES (0.75%) PER LINEAR INCH AND SHOULD BE MEASURED PER IPC-TM-650, METHOD 2.4.22.

7. ACCEPTABILITY PER ADI SPECIFICATION TST00115.

TOOLING:

8. IMPEDANCE REQUIREMENTS: IF NO STACKUP IS DEFINED, THE VENDOR IS ALLOWED TO ADJUST THE DIELECTRIC THICKNESS & TRACE WIDTHS TO MEET THE IMPEDANCE REQUIREMENT. IF SPECIFIED, THE VENDOR MUST MEET THE REQUIREMENTS LISTED IN THE IMPEDANCE TABLE. ANY ADJUSTMENT MADE TO THE DEFINED STACKUP, TRACE WIDTH & SPACING THAT IMPACT THE REQUIREMENTS MUST HAVE WRITTEN APPROVAL FROM ADI.

9. FILLET OPTIONS TO ENHANCE RELIABILITY AT PAD JUNCTIONS WHERE SPACING PERMITS.
 () FILLETS ALLOWED
 (X) FILLETS NOT ALLOWED

10. THIEVING:
- () VENDOR MAY ADD THIEVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS MAINTAINING A MINIMUM 0.100 INCH CLEARANCE FROM ALL COPPER FEATURES.
- () VENDOR MAY NOT ADD THIEVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS.

11. LAYER TO LAYER REGISTRATION SHALL BE WITHIN 0.003 INCHES.

FINISH:

12. DRILL SIZES ARE FINISHED HOLE SIZES. ALL HOLES SHALL BE LOCATED WITHIN 0.005 INCHES DTP, UNLESS SPECIFIED. MINIMUM BARREL PLATING OF 0.001 INCHES. PLATED HOLES SHALL NOT BE ROUGH OR IRREGULAR SO AS TO HINDER PROPER SOLDER WICKING. BARREL RELIEF ON SOLDERMASK ALLOWED IN UNFILLED VIA IN PAD HOLES.

13. PLATING SPECIFICATION:
(X) REFER TO LAMINATION DIAGRAM FOR FINISHED COPPER WEIGHT/THICKNESS REQUIREMENTS
THE STARTING COPPER WEIGHT/THICKNESS CAN VARY AS LONG AS THE FINISHED COPPER
WEIGHT/THICKNESS IS NOT LESS THAN THE SPECIFIED VALUE.

- ```

14. SURFACE FINISH:
 (X) IMMERSION GOLD (ENIG) 1.58-3.94 MICRO INCHES OVER 118-236 MICRO INCHES MIN. OF ELECTROLESS NICKEL PER IPC-452
 () OSP (ORGANIC SOLDERABILITY PRESERVATIVE)
 () IMMERSION SILVER
 () SOFT WIRE BONDABLE GOLD 30-50 MICRO INCHES OF SOFT WIRE
 BONDABLE GOLD OVER 100-150 MICRO INCHES OF NICKEL
 () EDGE CONNECTOR FINGERS ARE TO BE PLATED WITH 100 MICRO-INCHES(.0001") OF LOW STRESS
 NICKEL UNDER 30 MICRO-INCHES (.0003') OF GOLD
 () OTHER -----

```

15. SOLDERMASK:  
SOLDERMASK OVER BARE COPPER OR BARE GOLD (BOTH SIDES) TO MEET IPC-SM-840.  
IF PRESENT, DO NOT MODIFY SOLDERMASK DEFINED PADS (MASK OPENINGS LESS THAN COPPER PAD) WITHOUT APPROVAL.  
(X) LPI  
( ) OTHER \_\_\_\_\_

COLOR

- (X) GREEN  
( ) OTHER \_\_\_\_\_

16. APPLY SILKSCREEN TO BOTH SIDES USING A NON-CONDUCTIVE, EPOXY BASED INK PER ARTWORK.  
(X) WHITE  
( ) OTHER

TESTING:

17. FINAL ELECTRICAL TEST TO BE PERFORMED USING PROVIDED IPC-D-356A NETLIST OR ODB++ FORMAT FILE. THE PCB SHALL HAVE A VERIFICATION STAMP.

18. A TIME DOMAIN REFLECTOMETER REPORT (TDR) FOR EACH IMPEDANCE CONTROLLED LAYER & A CERTIFICATE OF COMPLIANCE SHALL BE PROVIDED BY VENDOR AT TIME OF SHIPMENT. INSTANCES WHERE TDR TESTING CAN'T BE PERFORMED BECAUSE THE TRACE LENGTH IS TOO SHORT ON THE OUTER LAYERS AT THE PIN ESCAPES IS ACCEPTABLE, ALL OTHER INSTANCES MUST BE REPORTED.

MISCELLANEOUS:

19. IF PRESENT, ALL BLIND/BURIED VIAS WITH AN ASPECT RATIO  $<1:1$  TO BE PLATED SHUT WITH COPPER WHEN USED AS VIA-IN-PAD OR AS A STACKED VIA. BLIND/BURIED VIAS WITH AN ASPECT RATIO  $>1:1$  TO BE FILLED WITH NON-CONDUCTIVE EPOXY.

20. FOR VIA FILL INFORMATION REFER TO DRILL CHART:  
 (X) NON-CONDUCTIVE EPOXY FILL ALL EQUAL TO OR LESS THAN 0.012 INCHES DRILLED VIAS  
 ( ) COPPER FILL ALL 0.XXXX INCHES DRILLED VIAS

21. INTENTIONAL SHORTS:  
IF AN INTENTIONAL SHORT REPORT IS SUPPLIED AND DOES NOT MATCH THE FAB DATA THEN  
ADI APPROVAL IS REQUIRED.

22. PEMNUTS:  
☐ PEMNUTS TO BE INSTALLED BY FABRICATOR  
☐ PEMNUTS NOT TO BE INSTALLED BY FABRICATOR  
☐ NOT APPLICABLE


23. MANUFACTURER ETCH/STAMP WITH PERMANENT NON-CONDUCTIVE INK  
ON SECONDARY SIDE UNLESS OTHERWISE SPECIFIED:  
A. UL CODE-FLAMMABILITY RATING FOR THOSE APPROVED MATERIALS(IF APPLICABLE)  
B. DATE CODE  
C. LOT NUMBER  
D. MANUFACTURER LOGO


25. PANELIZATION:  
BOARDS TO BE SHIPPED IN ARRAY AND KEPT INTACT  
PANEL TO BE SUBJECTED TO CUSTOMERS APPROVAL  
PANEL SOLDER PASTE STENCIL GERBER TO BE PROVIDED TO ANALOG

27. MINIMUM DESIGN LINE WIDTH IS .008INCH.  
28. MINIMUM DESIGN LINE SPACING IS .008 INCH.  
FAB NOTES REVISION: 2ND NOVEMBER 2022

| LAMINATION DIAGRAM                 |            |                             |                              |                                    |
|------------------------------------|------------|-----------------------------|------------------------------|------------------------------------|
| LAYER NUMBER                       | LAYER NAME | COPPER THICKNESS (OZ. INCH) | DIELECTRIC THICKNESS ( INCH) | MATERIALS                          |
| 1                                  | TOP        | 2 OZ. 0.0028" MIN           |                              | FINAL CU (THICKNESS AFTER PLATING) |
| 2                                  | LAYER_2    | 2 OZ. 0.0028" MIN           | 0.006                        | ISOLA 370HR/EQUIVALENT             |
| 3                                  | LAYER_3    | 2 OZ. 0.0028" MIN           | AS REQUIRED                  | ISOLA 370HR/EQUIVALENT             |
| 4                                  | BOTTOM     | 2 OZ. 0.0028" MIN           | 0.006                        | ISOLA 370HR/EQUIVALENT             |
| FINAL CU (THICKNESS AFTER PLATING) |            |                             |                              |                                    |

THE FINISHED PCB THICKNESS TO BE: 0.0625" +/- 0.010



|                                                 |  |  |                           |  |                                                                                                      |  |                                                              |  |     |
|-------------------------------------------------|--|--|---------------------------|--|------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------|--|-----|
| PRIMARY SIDE                                    |  |  |                           |  |                                                                                                      |  |                                                              |  |     |
| UNLESS OTHERWISE SPECIFIED<br>DIMENSIONS ARE IN |  |  | INCHES                    |  |  ANALOG DEVICES |  | WWM<br>DIVISION<br>804 WOBURN STREET<br>WILMINGTON, MA 01887 |  |     |
| TOLERANCES                                      |  |  | DECIMALS FRACTIONS ANGLES |  | DESIGNED BY<br>d d m m y y                                                                           |  | TITLE                                                        |  |     |
| XX . . .010 . . .1/32 . . . 2                   |  |  | HARDWARE SERVICES<br>X    |  | d d m m y y                                                                                          |  | FABRICATION                                                  |  |     |
| XXX . . .005                                    |  |  | HARDWARE SYSTEMS<br>X     |  | d d m m y y                                                                                          |  | EVAL - LT8643SA - AZ                                         |  |     |
| XXXX . . .0050                                  |  |  | TEST ENGINEER<br>X        |  | d d m m y y                                                                                          |  |                                                              |  |     |
| MATERIAL                                        |  |  | COMPONENT ENGINEER<br>X   |  | d d m m y y                                                                                          |  |                                                              |  |     |
|                                                 |  |  | TEST PROCESS<br>X         |  | d d m m y y                                                                                          |  |                                                              |  |     |
|                                                 |  |  | HARDWARE RELEASE<br>X     |  | d d m m y y                                                                                          |  |                                                              |  |     |
| FINISH                                          |  |  | DESIGNER<br>X             |  | d d m m y y                                                                                          |  | SIZE                                                         |  | REV |
|                                                 |  |  | PTD ENGINEER<br>X         |  | d d m m y y                                                                                          |  | FSCM NO                                                      |  |     |
|                                                 |  |  | CHECKER<br>X              |  | d d m m y y                                                                                          |  | DRAWING NUMBER                                               |  |     |
| DO NOT SCALE DWG                                |  |  |                           |  | D 24355                                                                                              |  | 09-082032                                                    |  | A   |
|                                                 |  |  |                           |  | SCALE 1/1                                                                                            |  | SHEET 2 OF 2                                                 |  |     |




| REVISIONS |                 |        |          |
|-----------|-----------------|--------|----------|
| REV       | DESCRIPTION     | DATE   | APPROVED |
| A         | INITIAL RELEASE | 220724 | X        |

ASSEMBLY NOTES:

- BOARD ACCEPTABILITY PER ANALOG DEVICES, INC. SPECIFICATION TST00119 (LATEST REVISION).
- REPAIRS PER IPC-7711/21(LATEST REVISION) ARE ALLOWED.
- REPAIRS ARE NOT ALLOWED IN SOLDERMASK FREE AREAS ON EITHER SIDE OF THE BOARD.
- INSTALL STANDOFFS AND TURRETS AS SHOWN BELOW:



- INSTALL INDUCTOR L1 AS SHOWN BELOW.













# SILKSCREEN PRIMARY

08-082032-03

REV A

LT8643SA  
42V, 6A SYNCHRONOUS  
STEP-DOWN SILENT SWITCHER2  
EVAL-LT8643SA-AZ


\* SEE USER GUIDE




# SILKSCREEN PRIMARY

08-082032-03


REV A



SOLDERMASK PRIMARY  
08-082032-04  
REV A




PASTEMASK PRIMARY  
08-082032-13  
REV A






L1 PRIMARY  
08-082032-01  
REV A




L2 GND PLANE  
08-082032-01  
REV A




L3 GND/SIGNAL

08-082032-02


REV A



L4 SECONDARY  
08-082032-02  
REV A




SOLDERMASK SECONDARY  
08-082032-06  
REV A



PASTEMASK SECONDARY

08-082032-14


REV A



# SILKSCREEN SECONDARY

## 08-082032-05

### REV A



## REV A

